PURITY Quell ST















PURITY QUELL ST – THE BEST WATER FOR GASTRONOMY

Technology: decarbonisation

Taste and function for gastronomy

Constant high performance in gastronomy is also expected from the high-quality machines. To ensure this performance can be used around the clock, it is advisable to work with optimised water.

The consistent water quality over the life of the filter and the reliable removal of unwanted taste and aroma elements ensures best quality and optimum aroma development for your drinks, as well as high machine protection.





IntelliBypass® technology

A largely volumetric-flow independent bypass water proportion ensures constant water quality, also for low water flow rates

Your advantages – great taste with reliable protection from limescale.

- Removal of unwanted taste and aroma elements in the complete filtrate (including in the bypass water)
- Coffee develops its full aroma

- Targeted adaptation to local conditions with variable bypass setting
- Limescale deposits and associated machine breakdowns are reduced
- Service and repair costs are clearly reduced

PURITY Quell ST

Consistently optimum water for different applications



Systematic filter technology

1. Pre-filtration

A fleece at the inlet reliably retains coarse particles and with its laminar water distribution ensures a high utilisation of the downstream filter medium.

2. Carbonate hardness reduction


The PURITY Quell ST filter medium reduces the content of carbonate hardness in a targeted way. As a result, unwanted limescale formation is prevented.

3. Activated carbon filtration

All of the water – including the bypass water – runs through an activated carbon filter. Taste and aroma elements that have a negative affect do not enter the filtrate

4. Fine filtration

At the end of the filtration process a fleece retains any fine particles.



The illustration serves as explanation of the filter technology. It is not to scale.

The PURITY promises:

Optimum water quality

Outstanding and consistent water quality – free of unwanted taste and aroma elements.

Maximum product safety

For uninterrupted operation and safe use.

Simple to use

Operation is simpler and easier than ever

The food safety of BRITA Professional water filter products is tested and monitored by independent institutes

Electronic components are CE-certified and labelled.



*applies to all materials in contact with water

Comparable capacity according to DIN 18879-1:2007: The comparable capacity is a standardised indicator to facilitate comparison of different filters. The comparable capacity is determined under extreme conditions. Normally the usable capacity in practical operation is clearly higher than the comparable capacity and may vary greatly depending on the usage conditions.

| than the comparable capacity and may vary greatly depending on the daage conditions. | | | | |
|--|-------------------------|---------------|---------------|--|
| Comparable capacity | 2,2401 | 4,4201 | 7,2531 | |
| Max. operating pressure | 6.9 bar | | | |
| Operating/water temperature | 4-30°C | | | |
| Flow at 1 bar pressure loss | max. 3501/h | | | |
| Nominal flow | 60I/h 120I/h | | | |
| Pressure loss at nominal flow | max. 0.12 bar | max. 0.36 bar | max. 0.32 bar | |
| Dimensions (height/width) | 408/249 mm | 520/249 mm | 550/288 mm | |
| Weight (dry/wet) | 10/12 kg | 12/15 kg | 18/24kg | |
| Connections (input/output) | G1"/G3/4" | | | |
| Operating position | horizontal and vertical | | | |

¹The capacities given have been tested and calculated on the basis of normal application and machine conditions. Due to external influences (e.g. variations in raw water quality and/or machine type), deviations from these results can occur.

| Products | Order number | | | |
|---|--------------|---------|---------|--|
| | 450 | 600 | 1200 | |
| New filter (complete system with filter cartridge) with measuring and display unit | 1009227 | 1009229 | 1009231 | |
| New filter (complete system with filter cartridge) without measuring and display unit | 1009228 | 1009230 | 1009232 | |
| Accessories | | | | |
| Replacement cartridge | 273000 | 273200 | 273400 | |
| BRITA FlowMeter 100-700 A | 298905 | | | |
| Carbonate hardness test kit | 710800 | | | |
| Appropriate hoses and hose sets from our comprehensive FlexConnect range as well as other accessories can be found in our price list. | | | | |
| Replacement parts | | | | |
| Pressure vessel lid with measuring and display unit | 272000 | | 272400 | |
| Pressure vessel lid without measuring and display unit | 272100 | | 272500 | |

Only drinking quality water may be used as the water supply for BRITA water filters.

BRITA Professional GmbH & Co. KG Heinrich-Hertz-Straße 4 D – 65232 Taunusstein

Phone: +49 (0) 61 28/7 46-57 65 Fax: +49 (0) 61 28/7 46-50 10

professional@brita.net www.professional.brita.de

